

Section 13
Joints





	DIN 71752 Steel, Zinc Plated Fork Heads		GN 751 Steel, Zinc Plated Fork Heads (Yokes)		GN 751-NI Stainless Steel Fork Heads (Yokes)
	GN 752 Steel Joint Pieces		GN 752-NI Stainless Steel Joint Pieces		GLRSW Stainless Steel Series K Spherical Plain Bearings
	GXSW Steel Series K Spherical Plain Bearings		DIN 648 Steel, Self-Lubricating Rod End Bearings -Tapped		DIN 648 A Steel, Self-Lubricating Rod End Bearings -Threaded Stem
	DIN 71802 Steel, Zinc Plated Angled Ball Joints		DIN 71802-NI Stainless Steel Angled Ball Joints		GN 710 Dust Caps for Angled Ball Joints
	GN 782 Steel Axial Ball Joints		GN 908 Steel Universal Joints		DIN 808-FB Steel Universal Joints with Friction Bearing
	DIN 808-NB Steel Universal Joints with Needle Bearing		GN 808.1 Cover Boots for Universal Joints		KM Metric Size, Bearing Lock Nuts
	MB Metric Size, Bearing Lock Washers		VBIP V-Belt Idler Pulleys		FIP Flat Idler Pulleys
	BSCA Bore, Shoulder and Clevis Adapters				

For complete technical information, CAD models and online buying, visit www.jwwinco.com