

Control Levers





Control Levers



LM
Plastic Control Levers



GN 750
Steel Control Levers



EN 623
Ergostyle® Plastic Control Levers



EN 512
Plastic Control Levers



WN 400
Plastic Fixed Clamping Levers



WN 400
Plastic Fixed Clamping Levers



DIN 99
Steel Clamping Levers



DIN 99-NI
Stainless Steel Clamping Levers




GN 99.5
Steel Clamp Nuts




GN 99.6
Stainless Steel Clamp Nuts



GN 99.7
Steel Double Arm Clamp Nuts



GN 99.8
Stainless Steel Double Arm Clamp Nuts



DIN 6337
Steel Ball Levers



GN 206
Malleable Iron Clamp Nuts



GN 206.1
Malleable Iron Double Arm Clamp Nuts



GN 211
Steel Control Levers



GN 212
Steel Tension Levers




GN 212-NI
Stainless Steel Tension Levers



DIN 6305
Steel Tommy Nuts Fixed Bar



GN 6304
Steel Tommy Screws Fixed Bar




DIN 6307
Steel Tommy Nuts Movable Bar



GN 6306
Steel Tommy Screws Movable Bar



GN 310
Steel Gear Lever Handles



GN 310-NI
Stainless Steel Gear Lever Handles



GN 150
Powdered Metal Split Hubs

For complete technical information, CAD models and online buying, visit www.jwwinco.com