



d	b (Tol. P9/JS9) Hub keyway	b (Tol. P9/N9) Shaft keyway	h	t ₁	t ₂	t ₃	t ₄
11	4	4	4	12.1	1.1 _{+0.1}	8	3 _{+0.1}
12	4	4	4	13.1	1.1	9	3
13	5	5	5	14.3	1.3	9.2	3.8
14	5	5	5	15.3	1.3	10.2	3.8
15	5	5	5	16.3	1.3	11.2	3.8
16	5	5	5	17.3	1.3	12.2	3.8
17	5	5	5	18.3	1.3	13.2	3.8
18	6	6	6	19.7	1.7	13.5	4.4
20	6	6	6	21.7	1.7	15.6	4.4
22	6	6	6	23.7	1.7	17.6	4.4
24	8	8	7	25.7	1.7 _{+0.2}	18.6	5.4 _{+0.2}
25	8	8	7	26.7	1.7	19.6	5.4
26	8	8	7	27.7	1.7	20.6	5.4
28	8	8	7	29.7	1.7	22.6	5.4
30	8	8	7	31.7	1.7	24.6	5.4
32	10	10	8	34.1	2.1	26	6
34	10	10	8	36.1	2.1	28	6
35	10	10	8	37.1	2.1	29	6
36	10	10	8	38.1	2.1	30	6
38	10	10	8	40.1	2.1	32	6
40	12	12	8	42.1	2.1	34	6
42	12	12	8	44.1	2.1	36	6
44	12	12	8	46.1	2.1	38	6
45	14	14	9	47.6	2.6	38.5	6.5
46	14	14	9	48.6	2.6	39.5	6.5
48	14	14	9	50.6	2.6	41.5	6.5
50	14	14	9	52.6	2.6	43.5	6.5

The above chart is to be used for coupling attachments type GN 000.4 and GN 000.5. Also required for clutch handwheels GN 321.4/5, GN 322.4/5, and GN 323.4/5.