



Part Number	Description	Radial Strength		Axial Strength		90 Degree Angled Strength	
		Maximum Working Load (N)	Breaking Load	Maximum Working Load (N)	Breaking Load	Maximum Working Load (N)	Breaking Load
6388010	C40/A Ø4.2	300	1960	150	1980	270	1480
6388020	C48/A Ø5.5	320	2620	320	2730	320	2570
6388030	C65/A Ø6.5	735	5400	540	4880	260	3900
6388040	C98/A Ø10.5	1190	9330	1100	7100	540	4230
6388100	C48/B M5	450	2980	420	3580	185	1510
6388110	C48/B M6	470	3200	380	3300	125	1620
6388120	C65/B M6	700	5540	655	4760	230	2330
6388130	C98/B M10	2170	15300	1020	7770	600	5320
6388200	C48/C M5x15	366	1920	380	2860	210	1720
6388210	C65/C M6x20	470	6600	530	6000	235	3250
6388220	C98/C M10x20	1770	15200	915	6220	480	3800