



d	b (Tol. P9/JS9) Hub keyway	b (Tol. P9/N9) Shaft keyway	h	t ₁	t ₂	t ₃	t ₄
7	2	2	2	8	1 _{+0.1}	5.8	1.2 _{+0.1}
8	2	2	2	9	1	6.8	1.2
9	3	3	3	10.4	1.4	7.2	1.8
10	3	3	3	11.4	1.4	8.2	1.8
11	4	4	4	12.8	1.8	8.5	2.5
12	4	4	4	13.8	1.8	9.5	2.5
13	5	5	5	15.3	2.3	10	3
14	5	5	5	16.3	2.3	11	3
15	5	5	5	17.3	2.3	12	3
16	5	5	5	18.3	2.3	13	3
17	5	5	5	19.3	2.3	14	3
18	6	6	6	20.8	2.8	14.5	3.5
20	6	6	6	22.8	2.8	16.5	3.5
22	6	6	6	24.8	2.8	18.5	3.5
24	8	8	7	27.3	3.3 _{+0.2}	20	4 _{+0.2}
25	8	8	7	28.3	3.3	21	4
26	8	8	7	29.3	3.3	22	4
28	8	8	7	31.3	3.3	24	4
30	8	8	7	33.3	3.3	26	4
32	10	10	8	35.3	3.3	27	5
34	10	10	8	37.3	3.3	29	5
35	10	10	8	38.3	3.3	30	5
36	10	10	8	39.3	3.3	31	5
38	10	10	8	41.3	3.3	33	5
40	12	12	8	43.3	3.3	35	5
42	12	12	8	45.3	3.3	37	5
44	12	12	8	47.3	3.3	39	5

The above chart is to be used for universal joint attachments DIN 808 and GN 908.